



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



### **Ophthalmic laser CARL ZEISS VISULAS YAG II (Reconditioned)**

Used, very good technical condition,  
Made in Germany,  
The specialised YAG II laser is used to perform e.g. capsulotomy and iridotomy,  
The set consists of the following parts:  
VISULAS YAG II laser:  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Power: 0.8/04 A max,  
Laser class 4,  
Wavelength: 1064 nm,  
Pulse length: < 4ns,  
Pulse types:  
Single: 10 mJ / 2 Hz,  
Double: 25 mJ / 0.5 Hz,  
Triple: 40 mJ / 0.25 Hz,  
9-step power adjustment,  
Lockable laser control unit and controller,  
With digital display,  
Menu in German language,  
Control unit dimensions: 17 x 13 x 36 cm,  
Slit lamp:  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Power: 40 W,  
Light source: 12 V / 30 W halogen bulb,  
Infinitely adjustable light intensity,  
Magnification eyepieces: 12,5 x,  
Focal length of lens f = 125 mm,  
Lamp magnification adjustment: 5x, 8x, 12x, 20x, 30x,  
Focus adjustment: -8 to +8D,  
Continuous slit width adjustment,  
Continuous adjustment of slit length,  
Infinitely adjustable chin height: 0-7 cm,  
Continuous adjustment of lamp up and down (joystick) within the range: 0-3 cm,  
Eyepiece and lamp rotatable by 90°,  
Patient handle,  
Dimensions of the lamp: 25 x 59 x 40 cm,  
The whole placed on Carl Zeiss table:  
Used, very good technical condition,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Power: 1.8 A,  
Continuous electric height adjustment in the range: 68 - 97,5 cm,  
Table top dimensions: 88 x 39 x 3 cm,  
Base: 87 x 67 cm,  
Included:  
Fixation point,  
Power cord,  
User manual in: PL, EN, DE (PDF),  
Overall dimensions: 97 x 160 x 68 cm,  
Weight: 53.5 kg,  
Has a current Technical Passport issued,  
Warranty:  
6 months for the national market - Poland,  
1 month for the international market,  
Financing options (Poland only): Installments, Leasing, Loan

