



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**Autoclave STATIM 6000B G4+ (New)**

New,  
Canadian production,  
Advantages:  
Small and very efficient class B autoclave for medicine,  
Sterilization chamber - pull-out drawer instead of cassette,  
Colour touch screen,  
Information management system - G4+,  
Electronic manual,  
LAN network operation,  
Compliance with EN13060 standard for sterilization of A and B type loads,  
Dedicated test cycles,  
Delayed start of cycles,  
Registration of cycles - recording in the autoclave memory,  
PACKAGE CONTENTS:  
Autoclave STATIM 6000B G4+,  
Built-in cycle recorder Data Logger,  
Tool tray,  
Packed instrument rack,  
Tool tray removal tool,  
Condensate bottle,  
Power cable,  
Water connection set,  
Flash drive,  
Ethernet cable,  
Chamber filter,  
HEPA biological filter,  
User manual in Polish,  
Technical data:  
Manufacturer: SCICAN,  
Country: Canada,  
Standards: PN EN 13060,  
Application of the autoclave: medical autoclave,  
CE certificate: yes,  
Notification to UDT: not required,  
Medical device certificate: yes,  
Operating language: Polish,  
Display: colour touch screen,  
Registration of cycles: Built-in recorder on pendrive,  
Sterilisation of batches type: B, S, N,  
Label printing: external printer (option - at extra charge),  
LAN operation: WiFi or RJ45 network cable,  
Network software: built-in, web browser,  
Chamber volume: 6l,  
Door locking: manual,  
Chamber dimension: 297.9 × 214.8 × 79.2 mm (L × W × H),  
Tray dimension: 297.9 × 214.8 × 79.2 mm (L × W × H),  
Maximum load capacity: 2.6 kg,  
Steam generator: outside the sterilisation chamber,  
Waste water container: yes,  
Container for distilled water: yes,  
External demineraliser: optional (at extra charge),  
Connection to mains water and sewage system: yes,  
Volume of appliance: > 60dB,  
Power consumption: range 0.6 kWh -1.0 kWh,  
External dimensions of appliance: 57.0 × 40.6 × 20.0 cm (L × W × H),  
Unit weight: 24 kg,  
Additional technologies:  
LAN monitoring and management,  
G4 CLOUD - cloud operation,  
Pre-programmed start-up,  
User profiles,  
Test reminder function (Vacuum - Helix / B&D - Vacuum + Helix / B&D),  
Weight of device: 24 kg,  
With valid technical passport,  
Warranty: 12 months,  
Finance options (Poland only): Instalments, Leasing, Loan,  
If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.  
WE SPEAK ENGLISH  
HABLAMOS ESPANOL  
WIR SPRECHEN DEUTSCH  
ON PARLE FRANCAIS  
WIJ SPREKEN NEDERLANDS  
МЫ ГОВОРИМ ПО РУССКИ  
МИ РОЗМОВЛЯЄМО УКРАЇНСЬКОЮ  
WE SHIP WORLDWIDE

