



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Dioptrimeter NIDEK LM - 350 (Reconditioned)

Used,

Technical condition: very good,

Visual condition: very good,

Japanese production,

Power supply: 230 V,

Frequency: 50/60 Hz,

Power: 15 W,

Nidek LM-350 is an instrument designed for measuring the focusing ability of lenses and optical systems,

The instrument guarantees simple measurement and precise centring of lenses,

Intuitive operation,

Equipped with:

240 V / 20 W bulb,

Green filter,

Specification:

Axis (AXIS) from 0 - 180°,

Operator lens: (-5) / 0 / 5 D,

Prism: 0 - 5 D,

Lens diameter: Ø 7 - 90 mm,

Possibility to change the tilt angle of the device in the range of 90° relative to its base,

The device has signs of use,

Incl. instruction manual in English (PDF),

Dimensions: 35 x 16 x 37 cm,

Weight: 5 kg,

Comes with a current Technical Passport issued,

Warranty:

6 months for the domestic market - Poland,

1 month for the international market,

Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN NEDERLANDS

МЫ ГОВОРИМ ПО РУССКИ

МИ РОЗМОВЛЯЄМО УКРАЇНСЬКОЮ

WE SHIP WORLDWIDE

