



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**NEOVO RX 22 G Medical monitor (New)**

- New,
- Constructed and proven for commercial video surveillance applications, the RX-22G display features AG Neovo's AIP technology, which provides adequate contrast, color and exceptional color fidelity. Equipped with EcoSmart Sensor and Anti-Burn-in™ technology, the energy-efficient RX-22G display consumes less than 0.5W in standby mode for uninterrupted, perfect performance. Greater versatility allows the installation of multiple RX-22G displays, in any surveillance configuration for security environments,
- Features and benefits of the NEOVO RX 22 G monitor:
  - Full HD 1920 x 1080 resolution,
  - Anti-Burn-in™ technology prevents ghosting in the image,
  - NeoV™ optical glass and durable metal housing provide superior clarity and protection,
  - PiP/PbP functions allow simultaneous viewing of images from multiple sources,
  - Image enhancement: de-interlacing/noise reduction/image rotation/framing,
  - Alink™ function for synchronized power on/off via HDMI,
  - Passive passive BNC output port,
  - RS232 control support for compatibility with control systems,
  - IP22 compliant on the front (IEC 60529 standard),
  - EcoSmart sensor detects ambient lighting conditions and automatically adjusts brightness level,
  - Black level adjustment to present more detail in dark images,
  - Gamma correction for improved clarity and color quality,
  - CCTV image mode for maximum detail and clarity in low-light conditions.
  - Night mode selection for dimming backlight levels in dark environments,
  - Locking OSD settings to prevent tampering in public areas,
  - Designed and developed for continuous 24/7 operation,
  - Plurality of inputs: DisplayPort, HDMI, DVI, VGA, S-Video, Composite,
  - Durable metal housing,
  - Also available in white,
- Specifications:
  - Matrix:
    - Panel type: LED-Backlit TFT LCD (TN Technology),
    - Diagonal: 21.5",
    - Max. Resolution: FHD 1920 x 1080,
    - Spot: 0.248 mm,
    - Brightness: 250 cd/m2,
    - Contrast Ratio: 20,000,000:1 (DCR),
    - Viewing angles (Pos/Pio): 170°/160°,
    - Color gamut: 16.7 M,
    - Response time: 3 ms,
  - Frequency (Pos/Pio):
    - Horizontal: 24 kHz - 83 kHz,
    - Vertical: 50 Hz - 75 Hz,
  - Inputs:
    - VGA: 15-Pin D-Sub x 1,
    - DVI: 24-Pin DVI-D x 1,
    - HDMI: 1,4 x 1,
    - DisplayPort: DisplayPort x 1,
    - Composite: BNC x 2,
    - S-Video: 4-Pin mini DIN x 1,
  - Outputs:
    - Composite: BNC x 2,
  - External Control:
    - RS232 In: 2.5mm Phone Jack,
  - Other Connections:
    - USB: 2.0 x 1 (Service Port),
  - Audio:
    - Input:
      - Stereo Audio Jack (3.5 mm),
      - Stereo Audio Jack (RCA),
      - Output: Stereo Audio Jack (RCA),
      - Internal speakers: 2W X 2,
  - Power supply:
    - Power supply: External,
    - Current: DC 12V, 2.1 A,
  - Power Consumption:
    - Power consumption: 16W (on),
    - Sleep mode: < 0.5W,
    - Off: < 0.3W,
  - NeoV™ optical filter:
    - Thickness: 3.0 mm (0.12"),
    - Reflectance ratio: < 1%,
    - Transparency factor: > 97%,
    - Surface hardness: 9H,
  - Operating Conditions:
    - Temperature: 0°C-40°C (32°F-104°F),
    - Humidity: 10%~90% (non-condensing),
  - Storage Conditions:
    - Temperature: -20°C-60°C (-4°F-140°F),
    - Humidity: 5%~95% (non-condensing),
  - Mounting:
    - VESA FPMPI: Yes (100 x 100 mm & 75 x 75 mm),
  - Stand:
    - Tilt: 0° to 17°,
  - Security:
    - Kensington™ security slot: Yes,
  - Dimensions:
    - Product with stand (W x H x D): 513.2 x 368.5 x 155.0 mm (20.2" x 14.5" x 6.1"),
    - Product without base (W x H x D): 513.2 x 324.3 x 56.2 mm (20.2" x 12.8" x 2.2"),
    - Package (W x H x D): 614.0 x 477.0 x 204.0 mm (24.2" x 18.8" x 8.0"),
  - Weight:
    - Monitor without stand: 6.0 kg( 13.2 lb),
    - Monitor with base: 6.7 kg( 14.8 lb),
    - Monitor with packaging: 8.8 kg( 19.4 lb),
  - Regulatory Compliance:
    - Declarations and Directives: CE, WEEE, RoHS, REACH, BSMI, CB, FCC, CCC,
    - Power supply certifications: Delta /ADP-40DD-B: CE, cUL/UL, RCM, WEEE, KCC, BSMI, EAC,
  - Accessories:
    - Supplied with the monitor; power adapter, power cord, VGA cable, audio cable, quick start guide, warranty card,
  - Optional accessories (at extra charge):
    - Table mount: DMC-01, DMC-02D, DMS-01D, DMS-01Q, ES-02,
    - Ceiling mount (horizontal only): CMP-01 + WMK-03,
    - Wall mounts (horizontal only): WMA-01, WMK-01, WMK-03, PMK-01,
- Has a current Technical Passport issued,
- Warranty 36 months,

If you have any questions, please do not hesitate to contact us!  
In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

