



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **SOLIS 60 C ceiling examination light (New)**

- New,
- Made in Poland,
- A lamp for ceiling mounting,
- Advantages and features of SOLIS 60 C lamp:
  - Circular reflector designed to accurately illuminate the working field and eliminate any shadows,
  - Features a sterilizable, handy handle that makes it easy to adjust its position,
  - The illuminating body, ultra-flat to not disturb the operator, is equipped with a durable polycarbonate screen that provides protection against possible accidental hits,
  - The position of the SOLIS 60 lamp can be easily changed thanks to its ability to rotate around 4 axes: the design provides the ability to come a full circle without stopping,
  - The arm moves vertically thanks to a spring-compensated balancing device,
  - The spotlight can be rotated along the vertical and horizontal axes,
  - The lamp guarantees 60,000 lux of light at a distance of 1 m, providing ideal illumination for all medical specialties,
  - The handy and space-saving design makes the SOLIS 60 ideal for diagnostic applications, surgery preparation rooms, and research laboratories,
  - Thanks to the innovative "touchless" control, the operator can adjust the light intensity according to his needs,
- Technical specifications:
  - Power supply voltage: 24V DC,
  - Illuminance at a distance of 1m ( $E_c$ ): 60,000 lux,
  - Adjustable illumination intensity: non-contact 50 ÷ 100%,
  - Color rendering index Ra: 96,
  - Color temperature: 4400 K,
  - Working field diameter  $d_{10}$ : 210 mm,
  - Working field diameter  $d_{50}$ : 105 mm,
  - Adjustable working field diameter: NO,
  - Temperature increment in the surgeon's head area: < 1°C,
  - Depth of illumination  $L_1 + L_2$ :
    - 20%: 194 cm,
    - 60%: 130 cm,
  - Power consumption of the luminaire: 20W,
  - Number of light sources: 18 LED,
  - Insulation class: I,
  - Degree of protection of the housing: IP 43,
  - Service life of the light source up to 60,000 h,
- Valid technical passport issued,
- Warranty 24 months,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN DUTCH

Мы говорим по русски

Мы говорим по украински

