



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



NIDEK LM-350 Diopter (Reconditioned)

- Used,
- Technical condition: very good,
- Visual condition: very good,
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 15 W,
- Nidek LM-350 is an instrument designed to measure the focusing ability of lenses and optical systems,
- The device guarantees simple measurement and precise centering of lenses,
- Intuitive operation,
- Equipped with:
 - 240 V / 20 W incandescent lamp,
 - Green filter,
- Specifications:
 - Axis in the range of 0 - 180°,
 - Operator lens: (-5) / 0 / 5 D,
 - Prism: 0 - 5 D,
 - Lens diameter: Ø 7 - 90 mm,
 - Possibility to change the angle of the device in the range of 90° with respect to its base,
- Included:
 - User manual in English (PDF),
- Dimensions: 35 x 16 x 37 cm,
- Weight: 5 kg,
- Cat 02,
- Valid technical passport issued,
- Warranty:
 - 6 months for domestic market - Poland,
 - 3 months for the international market,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN DUTCH

Мы говорим по русски

Мы говорим по украински

