



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67  
E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006  
[kw@praiston.pl](mailto:kw@praiston.pl)



## **SONY DVO - 1000MD DVD recorder (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in England,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 0.56 - 0.28 A,
- Sony recorder is a small, durable and easy-to-use digital data archiving device,
- Product features:
  - Enables video recording and playback in a wide range of visible light and other modes,
  - Hard drive provides additional protection for recordings in case of power loss,
  - Can record up to 3 h on a single disc,
  - Recording on DVD-RW discs,
  - DVOFAST function allows the operator to eject the disc in less than 2 minutes after recording without finalizing the disc,
  - Freeze mode allows the operator to set a frame or field as the first image,
  - Convenience of browsing through recordings thanks to an automatically created list displayed by pressing the LIST button on the unit's front,
  - RS - 232C connector allows remote control with other devices and video playback at 30x speed,
  - Option to switch between PAL and NTSC from the menu,
  - Keypad on the control panel and menu in English,
- Specifications:
  - Recording modes:
    - HQ mode: 60 min,
    - SP mode: 120 min,
    - LP mode: 180 min,
  - Recording format:
    - Video: MPEG - 2,
    - Audio: Dolby Digital,
  - Recording medium: DVD + RW,
  - Media recording speed: 2.4 x, 4 x,
- Equipped with various kinds of inputs and outputs:
  - Analog VIDEO inputs and outputs:
    - VIDEO IN - OUT: 3 BNC sockets (including 2 for VIDEO IN),
    - S-VIDEO IN - OUT: 3 4 - pin DIN sockets (including 2 for S - VIDEO IN),
  - AUDIO analog inputs and outputs:
    - AUDIO IN - OUT: 4 jack sockets for right and left channels,
    - AUDIO MONITOR: 1 jack socket,
  - PILOT 1: stereo mini jack socket for SVRM - 100A remote control (no remote control included),
  - PILOT 2: mini jack socket for foot switch (no switch included),
  - Digital signal socket and LINK (DV IN),
  - RS - 232C socket,
  - USB 2.0 socket,
- Included:
  - User manual in English (PDF),
  - Power cord,
- Dimensions: 21.5 x 13 x 39 cm,
- Weight: 6 kg,
- Cat 03,
- Valid technical passport issued,
- Warranty:
  - 6 months for domestic market - Poland,
  - 3 months for the international market,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

WE SPEAK ENGLISH

HABLAMOS ESPANOL

WIR SPRECHEN DEUTSCH

ON PARLE FRANCAIS

WIJ SPREKEN DUTCH

Мы говорим по русски

Мы говорим по украински

