



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



TW1080 dioptrimeter (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in China,
- Power supply: 230 V,
- Frequency: 50-60 Hz,
- Power: 40W,
- **TW1080 dioptrimeter** is characterized by very easy operation, high quality production, and fast and accurate measurement,
- Fully functional: it can measure spherical and cylindrical lenses, bifocal and trifocal lenses, progressive lenses (PPL), contact lenses (CL) and colored lenses (sunglasses) with transmittance of more than 10%,
- PD measurement,
- An in-built thermic printer (paper size 38 mm),
- LCD black and white screen with 320 x 240 px size,
- Specification (measurment range):
 - sphere: from 0 to to $\pm 25D$ (step: 0.01D, 0.12D, 0.25D),
 - cylinder: from 0 to 10D (step: 0.01D, 0.12D, 0.25D),
 - axis: from 0 to 180° (step: 1°),
 - adduction: from 0 to 10D (step: 0.01D, 0.12D, 0.25D),
 - prisms: from 0 to 10 Δ (step: 0.01 Δ , 0.12 Δ , 0.25 Δ),
 - PD: up to 80mm,
 - lens diameter: up to 120mm,
 - Abbe constant: from 20 to 60,
 - contact lens: from 0 to 25D, BC 6.00 to 9.00
- **English menu,**
- **In the set:**
 - Power cord,
- Dimensions: 22 x 27 x 42 cm,
- Weight: 7 kg,
- **It has up-to-date overview and is ready to work,**
- **Provided with a 12-month valid Technical Passport (service report),**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

