



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



ESAOTE MYLAB OMEGA USG device (Ex-Display)

- A new, post-display product,
- **Real photos of the product,**
- Made in Italy (2019),
- **Bought on 11.05.2022, in use since 06.2022 to 12.2022,**
- Power supply: 230 V or via an in built battery,
- Frequency: 50/60 Hz,
- **Esaote MyLab Omega** is a high-class, portable, multidisciplinary ultrasound scanner with an innovative and ergonomic design,
- Advanced diagnostic device with a very high level of imaging in both 2D and Doppler modes,
- Dedicated to any type of medical activity, it will also be perfect for: radiology and orthopedics,
- English menu of the device,
- English keyboard on the control panel,
- **Device's advantages:**
 - Has the ability to observe micro-fluids,
 - Portable so it can be easily transported to the patient,
 - It has exceptional flexibility with its unique in-built 15.6" Full HD touchscreen and rotating and tilting monitor,
 - Fast and easy operation,
 - Zero-click automation,
 - Extensive connectivity,
 - Complete advanced clinical tools,
 - Two probe ports,
 - Built on new engine and supported by Windows 10,
 - In built ports:
 - LAN RJ45,
 - USB – 4 pieces,
 - Video output: HDMI,
- **Imaging modes:**
 - 2D,
 - M,
 - CDI (Color Doppler),
 - PDI (Power Doppler),
 - PW (Pulsed Doppler),
 - Dual mode,
 - THI (Harmonic Imaging),
 - MikroV,
 - X flow,
 - Xview+,
 - Dicom,
- **The device is equipped with:**
 - **A mobile cart:**
 - Height regulation,
 - Holders for probes and gels,
 - Comfortable carrying handle,
 - Shelf for accessories,
 - Four double wheels with brakes,
 - **MITSUBISHI P95DE Videoprinter** - is a high-speed, high-resolution digital monochrome thermal printer,
 - **Specification:**
 - Long-lasting print heads,
 - Thermal printing - true photorealism - 256 grayscale degrees,
 - Roll Type technology - printing on 110 mm wide roll paper,
 - Print size: 100 x 75 mm (standard),
 - Print speed: 1.9 seconds,
 - Print resolution: 325 PPI,
 - Printing with 2 or 4 parts, Multiimage for each format,
 - Print output: 254 prints per page size (1280 x 960),
 - Function menus shown on LED display,
 - English menu on the control panel,
 - Printing of setting parameters under the photo,
 - Paper saving mode (260 Normal prints from roll),
- **In the set:**
 - Linear head SL 2323,
 - Linear head wide L4-15,
 - Convex AC2541 head,
 - English instruction manual (PDF),
 - 19 V, 9.47 A, 180 W AC/DC power supply,
 - Power cord,
- Dimensions:
 - Of the device in an operating position: 40 x 38 x 36 cm,
 - With a cart: 68 x 52 x 114-143 cm,
- Device's weight with batteries: ok. 7,6 kg,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport and ready to work,**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

