



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



AQUATEC ORCA electric bathtub lifter (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Germany (2020),
- Power supply: via one in-built Li-Ion 10,8 V 2150 mAh battery,
- Frequency: 50/60 Hz,
- Power: 4 A,
- **Aquatec Orca** is an electrically powered bath lift that enables comfortable and relaxing bathing for people who are unable to get into and/or out of the tub on their own,
- It was created with the thought of the elderly and disabled,
- Technically, it fits any type of bathtub,
- A simple control system using a wired remote control ensures easy operation and allows people with limited mobility to increase their independence,
- **Product's characteristics:**
 - Controlled by an ergonomic remote control that stays on the water,
 - Optimally shaped bottom plate, providing more space in the bath,
 - Elevator base equipped with rubber suction cups that prevent the device from moving in the bath,
 - A backrest that can be tilted up to 40 degrees,
 - Smooth surface that can be easily and quickly cleaned,
 - Foldable design, optimal dimensions and low self-weight make Aquatec easy to fold and store,
- **Specification:**
 - Voltage 14 V
 - Rated current 4 A
 - Lilon battery type
 - Charger input 230-240V AC, 50Hz
 - Charger output 24V DC, 200mA, 12W
 - Charging time with low voltage warning approx. 5 hours
 - Seat length 590 mm
- **In the set:**
 - Set of removable covers,
 - Wired remote control,
 - Polish instruction manual (PDF),
 - Power cord,
- Dimensions:
 - Seat width with side flaps open: 71.5 cm,
 - Seat width with side flaps folded: 39 cm,
 - Seat height in lowest position: 6 cm,
 - Seat height in highest position: 42 cm,
 - Overall:
 - When unfolded: 62 x 71,5 x 108 cm,
 - When folded: 62 x 39 x 24 cm,
- Maximum load: 135 kg,
- Set's weight: 12 kg,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport and ready to work,**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

