



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



UZUMCU PA-1R transport suction (Ex-Display)

- A new, post-display product,
- Technical condition: perfect,
- Visual condition: perfect,
- **Real photos of the product,**
- Made in Turkey, (2014),
- Power supply: 230 V or via 12V battery and a car lighter socket,
- Częstotliwość: 50/60 Hz,
- **UZUMCU PA-1R transport suction,**
- **Specification:**
 - Vacuum generated 620 mmHg (0.83 bar),
 - Capacity max. 20 l/min,
 - Max. noise 55 dB,
 - Suction pump power 0.12 kW,
 - Battery life is 20 min at maximum suction power,
 - Full charge time is 80 min,
- **In the set:**
 - Power charger,
 - Car charger,
 - Silicone hose (2m),
 - Silicone hose (50 cm),
 - Antibacterial filter,
 - Autoclavable jar with 2 L capacity,
 - A mobile tripod,
- Dimensions:
 - Of the suction: 36,5 x 16 x 34,5 cm,
 - Overall: 106 x 54 x 54 cm,
- Weight: 9,5
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport and ready to work,**
- **Guarantee:**
 - **6 months for the domestic market (Poland),**
 - **3 months for the international market,**
 - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

