



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



ANTAR AT52304 a foldable, electric wheelchair (New)

- A brand new product,
- **Real photos of the product,**
- Made in Germany (2022),
- Power supply: 230 V,
- Power supply via one, new in-built Li-ion 24 V 12 Ah battery,
- Frequency: 50/60 Hz,
- Power: 250 W,
- **Antar AT52304** is an electric wheelchair that will facilitate the functioning of the elderly, sick or disabled,
- **Product's characteristics:**
 - The wheelchair will easily fit even in small car boots, because it has:
 - Foldable cross frame, making storage and transportation much easier,
 - Tilttable and removable footrests,
 - Foldable (breakable) backrest,
 - Tilttable armrests, making it easy to move around,
 - Amortized front wheel forks,
 - Control panel - joystick can be mounted on the right or left side,
 - Two manual levers to stop the wheelchair,
 - **The control panel has:**
 - Battery charge indicator,
 - Speed increase and decrease button,
 - Horn,
 - On/off wheelchair switch,
 - Speedometer - 5 gears,
 - Inflatable wheels: back 12", front 8",
 - Anti-turn wheels for increased safety,
- **Specification:**
 - Total width: 67 cm,
 - Total length: 100.5 cm,
 - Length without footrests: 78 cm,
 - Total height: 96 cm,
 - Seat height from the ground: 52 cm,
 - Seat width: 45 cm,
 - Seat depth: 45 cm,
 - Dimensions when folded: height: 73 cm x width: 44 cm,
 - Armrest height: 20 cm,
 - Maximum speed: 6 km/h,
 - Braking distance at 6 km/h: ≤ 150 cm,
 - Max. turning radius: ≤ 120 cm,
 - Approximate range on a single charge: 20 km,
 - Maximum elevation angle: 6 deg.
 - Front wheel: tires that do not require inflation, outer diameter 19 cm,
 - Back wheel: pneumatic tires, outer diameter 40.6 cm,
- **In the set:**
 - Polish instruction manual (PDF),
 - 24 V 2A charger,
 - Set of accessories shown in the last photo,
- Maximum load: 120 kg,
- Weight:
 - Of the battery: 2,5 kg,
 - Of the wheelchair with the battery: 36 kg,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport (service report),**
- Financing possibilities (Poland only): Installments, leasing, loan,

