



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**CARL ZEISS KSK 150-FC colposcope (vision track) (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 150 VA,
- **ZEISS KSK 150-FC** is a mobile colposcope equipped with a vision track,
- Light source: halogen bulb 12V / 100W,
- Smooth regulation of light intensity,
- Optical fiber,
- Green filter,
- Magnification: 0.4x, 0.6x, 1x, 1.6x, 2.5x,
- Focal length (f): 250,
- Eyepiece: 20x,
- Smooth regulation of:
  - Eyepiece height in the range of 74 -120 cm,
  - Eyepiece spacing with knobs,
- There are knobs on the pantograph arm to lock it in the selected position,
- **The colposcope is expanded with a vision track that includes a:**
  - **CANON Model EOS M3 video recorder:**
    - It has a 22.3 x 14.9 mm CMOS sensor with 24.2 MP resolution,
    - Large, bright touchscreen provides clear images,
    - Simple function control and excellent low-light performance for capturing high-quality images,
    - Image processor: DIGIC 6,
    - Focus control: Hybrid CMOS AF II,
    - ISO sensitivity: 100 - 12800,
    - Auto white balance set by the sensor,
    - 3" sRGB Clear View LCD II touch screen,
    - 3:2 aspect ratio,
    - Menu to be chosen in: PL, EN, DE, FR, ES, RU, PT, CS, IT, FI, NL, SV, NO, HU, DA, TR, RO, AR,
    - Support for SD, SDHC, SDXC cards,
    - Video: Full HD, 30 fps,
    - Images: RAW, JPEG,
  - **FUJITSU E22T-7 monitor:**
    - Monitor diagonal: 21,5",
    - Resolution: 1920 x 1080 px,
    - Dimensions: 52 x 31 x 6 cm,
    - Placed on a movable arm,
    - Has the following inputs and outputs:
      - D-Sub (VGA),
      - DVI,
      - HDMI,
      - SPEAKER,
- Mobile, on a 5 - arm mobile base with wheels, including 2 with a brake,
- **In the set:**
  - CANON 7.2 V / 1040 mAh battery for camera,
  - NEWELL LP-E17 7.2 V / 950 mAh battery for camera,
  - 16GB microSD card,
  - SDHC + wi-fi adapter,
  - HDMI mini cable,
  - LC-E17E charger,
  - Newell USB charger,
  - Colposcope user manual in English (PDF),
  - Camera user manual in Polish (PDF),
  - Power cord,
- Overall dimensions: 90 x 65 x 132 cm,
- Weight: 57 kg,
- Cat 06,
- **It has up-to-date overview and is ready to operate,**
- **Provided with a 12-month valid Technical Passport (service report),**
- **Guarantee:**
  - **6 months for the domestic market (Poland),**
  - **3 months for the international market,**
  - **Possible guarantee extension for extra fee, up to 12 months for both, domestic and international market,**
- Financing possibilities (Poland only): Installments, leasing, loan,

