



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**SCICAN BRAVO 17V Class B autoclave (Ex-Display)**

- New (ex-display),
- Technical condition: perfect,
- Visual condition: perfect,
- Real photos of the product,
- Made in Canada, (2016),
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 2300 W,
- Autoclave SCICAN BRAVO 17V - fast sterilization cycles, ease of use and autonomous operation allow to use this autoclave for sterilization of all types of instruments in any medical practice and clinic. The traditional cylindrical chamber with a mobile rack gives great possibilities for its arrangement making the autoclave even more versatile,
- The autoclave has a cylindrical chamber made of a single sheet, the highest quality stainless steel. The lack of welded elements clearly affects the durability of the chamber and the ease of keeping it clean,
- The useful capacity of the chamber, is about 9 liters. The usable space in the chamber is limited by the rack and trays, that is, we are dealing with a cuboid inscribed in a cylinder,
- Steam is produced in a generator located outside the autoclave chamber. As a result, the time required to start the sterilization process is significantly reduced and the conditions of the process itself are improved,
- The chamber door is opened and closed automatically. This is a very comfortable solution, directly affecting the quality of daily operation of the autoclave,
- Autoclave BRAVO 17V is equipped with a large, graphic LCD display presenting in Polish the current status of the device.
- The BRAVO 17V autoclave is equipped with a large, graphic LCD display presenting in Polish the current status of the device as well as enabling its trivial operation,
- The user has at his disposal four multifunctional buttons, by means of which he can easily select and start the sterilization processes as well as change the autoclave settings,
- The autoclave has a built-in system for electronic recording of sterilization cycles. One of the most user-friendly systems. Cycles are recorded on a USB interface pendrive connected to the autoclave.
- It works in a single water cycle system. This means that fresh distilled water is used for each sterilization cycle. The device has a built-in distilled water tank and a built-in condensate tank. This gives the autoclave a high degree of autonomy in operation. It can be placed almost anywhere in the office or clinic. The autoclave optionally has the ability to draw water from the mains water supply through a demineralizer and drain the condensate to the sewer,
- Specifications:
  - Cycle recording: digital,
  - Cycle for packaged. + 134C drying: 38 min,
  - Cycle for non-packaged. + 134C drying: 31 min,
  - Quick cycle for non-packaged without drying: 12 min,
  - Sterilization of batches of type: A and B,
  - Total chamber volume: 17 l
  - Usable chamber volume: approx. 9 l
  - Distilled water tank capacity: 2 l
  - Condensate tank capacity: 2 l
  - External demineralizer: Yes (optional),
  - Connection to the canal,
  - Connection to sewer: Yes (optional),
  - Operating volume: 58 dB,
- Menu in Polish,
- Included:
  - English user manual (PDF),
  - 2 x mesh trays,
  - Tray holder,
  - Drain hose,
  - Flash drive,
- Dimensions:
  - Overall: 48 x 42 x 56 cm,
  - Chamber: 25 cm diameter x 35 cm depth,
  - Trays: 27 x 17 x 2 cm,
- Weight: 58 kg
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,
- Valid technical passport issued,

If you have any questions, please do not hesitate to contact us!  
In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.  
WE SPEAK ENGLISH  
HABLAMOS ESPANOL  
WIR SPRECHEN DEUTSCH  
ON PARLE FRANCAIS  
WIJ SPREKEN DUTCH  
Мы говорим по русски  
Мы говорим по украински

