



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **STIRLING ULTRACOLD SU105UE Low temperature freezer (Ex-Display)**

- Post-exchange (new),
- Technical condition: perfect,
- Visual condition: perfect,
- Real photos of the product,
- Made in USA, (2021),
- Power supply: 230 V,
- Emergency power supply: via 1/2 built-in batteries..... - replaced or can be replaced with new ones at additional cost,
- Frequency: 50/60 Hz,
- Power: 300 W
- STIRLING ULTRACOLD SU105UE is designed for low power consumption and high energy saving,
- Wide temperature range in the range: -20 °C / - 86 °C,
- Refrigerator equipped with innovative Stirling pistonless motor,
- Technical specifications:
  - Internal capacity: 105 liters,
  - Ability to accommodate 72 boxes of 2"(inches),
  - Touch screen control,
  - Fully adjustable warning and alarm timers,
  - Event log system (alarms, doors opened),
  - Temperature memory within 30 days,
- Temperature range:
  - From -20 °C to -86 °C (at 32 °C ambient temperature),
  - From -80 °C to -60 °C (Time: 2 hours),
  - From -80 °C to -40 °C (Time: 5.2 hours),
  - Return to constant temperature after opening the door at -80 °C: (40 minutes),
  - Achieving -80 °C at an ambient temperature of 25 °C (Time: 9 hours),
- Adjustable in 1 °C increments,
- Recommended ambient temperature for optimal refrigerator operation: +5 °C to + 35 °C,
- Built-in emergency 6-volt battery to support the touch screen for 12 h,
- English language menu,
- Included:
  - User manual in English(PDF),
  - Power cord,
  - Mounting shelf,
  - Door opening keys: 2 pcs,
- Dimensions:
  - Internal: 53 x 43 x 45 cm,
  - External: 86 x 71 x 68 cm,
- Weight: 84 kg,
- It has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

