



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



CARL ZEISS KSK 150-FC Colposcope (with vision track) (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 150 VA
- ZEISS KSK 150-FC is a mobile colposcope equipped with a vision track,
- Advantages:
 - Sophisticated optical performance,
 - One-handed operation - it has several different control knobs gathered close together, so operator can adjust the field of view, magnification or focus with one hand using the left or right handle,
 - Colposcopy and hysteroscopy in one system,
 - Digital documentation - recording colposcopic and hysteroscopic images with a digital camera,
- Technical specifications of ZEISS KSK 150-FC:
 - Light source: halogen bulb 12V / 100W,
 - Infinitely adjustable light intensity,
 - Light guide,
 - Blue filter,
 - Magnification: 0.4x, 0.6x, 1x, 1.6x, 2.5x,
 - Focal length (f): 250,
 - Eyepiece: 12.5x,
 - Infinitely adjustable:
 - Eyepiece height from 74 -120 cm,
 - Eyepiece spacing by means of knobs,
 - There are knobs on the pantographic arm to lock it in the selected position,
- Colposcope expanded with a vision track, which includes:
 - Microscope camera:
 - Sensor: 34 million pixels CMOS,
 - Interface: HDMI (type A). USB (type B). small memory card,
 - HDMI image resolution: 34 MP,
 - Video resolution: 2K at 30 fps 1080p at 60 fps,
 - HDMI resolution: 1920x1080p 60 frames per second,
 - HDMI scale: screen support 4: 3,16: 9,16: 10,
 - USB 2.0 (without drive): 1920 x 1080 at 30 fps 1280 x 720 at 30 fps 640 x 480 at 30 fps,
 - Camera remote control for wireless video control,
 - TF card - 16 GB,
 - ACL OR-PC 21LP medical computer with built-in monitor:
 - It has the following inputs and outputs:
 - LINE OUT,
 - MIC,
 - LAN - 2 pcs,
 - USB 2.0 - 2 pcs,
 - USB 3.0 - 2 pcs,
 - COM 1 and 2,
 - HDMI 1 and 2
 - Specifications:
 - Resolution: 1920 x 1080 px,
 - Contrast ratio 1000:1,
 - Brightness 250 cd/m²,
 - Viewing angle: 178°/178°,
 - Processor: IntelCore i5,
 - RAM: 10 GB,
 - System: Windows 10 Pro,
 - 128 GB SSD,
 - Light source:
 - Olympus CLH-SC:
 - Light source: 150 W halogen lamp,
 - Lamp life: about 50 hours of continuous operation,
 - Infinitely adjustable light intensity,
- Construction operating on a mobile base equipped with 5 casters (2 braking),
- Installed dedicated camera software HAYER 4.10,
- Installed miniIRIS software in DEMO version - possibility to upgrade the program to full version - at additional cost,
- Menu in language: PL - possibility to install any language,
- Included:
 - Power cord,
 - User manual in: English (PDF),
 - MICROSOFT all-in-one wireless keyboard equipped with trackpad,
 - 3 segment control foot switch,
 - Wireless remote control for controlling the camera,
- Dimensions:
 - Overall: 77 x 70 x 133 cm,
 - Base : Ø 70 cm,
- Weight : 60 kg,
- Cat 07,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

