



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



CARL ZEISS KSK 150-FC Colposcope (vision track) (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 180 VA,
- ZEISS KSK 150-FC is a mobile colposcope equipped with a vision track,
- Light source: halogen bulb 12V / 100W,
- Infinitely adjustable light intensity,
- Fiber optic,
- Green filter,
- Magnification: 0.4x, 0.6x, 1x, 1.6x, 2.5x,
- Focal length (f): 250,
- Eyepiece: 10x,
- Infinitely adjustable:
 - Eyepiece height from 74 -120 cm,
 - Eyepiece spacing by means of knobs,
- There are knobs on the pantographic arm to lock it in the selected position,
- Colposcope expanded with a video track, which includes:
 - CANON Model EOS M3 Camera:
 - Features a 22.3 x 14.9 mm CMOS sensor with 24.2 MP resolution,
 - Large, bright touchscreen provides clear images,
 - Simple function controls and excellent low-light performance for capturing high-quality images,
 - Image processor: DIGIC 6,
 - Focus control: Hybrid CMOS AF II,
 - ISO sensitivity: 100 - 12800,
 - Auto white balance set by the sensor,
 - 3" sRGB Clear View LCD II touch screen,
 - 3:2 aspect ratio,
 - Selectable menus in PL, EN, DE, FR, ES, RU, PT, CS, IT, FI, NL, SV, NO, HU, DA, TR, RO, AR,
 - Support for SD, SDHC, SDXC cards,
 - Video: Full HD, 30 fps,
 - Images: RAW, JPEG,
 - FUJITSU E22T-7 Monitor:
 - Monitor diagonal: 21,5",
 - Resolution: 1920 x 1080 px,
 - Dimensions: 52 x 31 x 6 cm,
 - Placed on a movable arm,
 - Has the following inputs and outputs:
 - D-Sub (VGA),
 - DVI,
 - HDMI,
 - SPEAKER,
- Mobile, on a 5-arm mobile base with casters, including 2 with brakes,
- Includes:
 - CANON battery for the camera 7.2 V / 1040 mAh,
 - NEWELL LP-E17 battery for camera 7.2 V / 950 mAh,
 - L39/M3 lens adapter,
 - 16GB microSD card,
 - SDHC + wi-fi adapter,
 - HDMI mini cable,
 - Newell USB charger,
 - Colposcope user manual in English (PDF),
 - Camera manual in Polish (PDF),
 - Power cord,
- Overall dimensions: 90 x 70 x 130 cm,
- Weight: 54 kg,
- Cat 08,
- Has a current Technical Passport issued,
- Warranty:
 - 6 months for domestic market - Poland,
 - 3 months for the international market,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!
In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

