



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **LUMENIS SL-990 Slit lamp (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Italy,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Light source: halogen bulb 6 V / 20 W,
- LUMENIS SL990 is a slit lamp for examining the structures of the eye,
- It features multiple anti-reflective layers, which improves optical resolution and contrast,
- Technical specifications:
  - Eyepiece correction: (-5) / 0 / 5,
  - Magnification change: stepwise,
  - Magnifications: 10, 16,
  - Focal point,
- Adjustment:
  - Slit rotation in the range of 180°,
  - Rotation of the light source within 180°,
  - Infinitely adjustable light source intensity,
  - Patient's chin within 6.5 cm,
  - Eyepiece spacing,
- It has the following filters:
  - Blue,
  - Red,
  - Transparent filter,
  - Gray filter,
  - Green filter,
- Slit lamp on a mobile table:
  - Adjustable in height from:
    - 68 - 93 cm,
  - On 4 casters (2 braking),
- Included:
  - Power cord,
- Overall dimensions: 80 x 38 x 136 cm,
- Weight: 42.5 kg,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

