



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



CARL ZEISS KSK 150-FC Colposcope (4K vision track) (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 180 VA,
- Halogen bulb: 12 V / 100 W,
- CARL ZEISS 150-FC is a mobile colposcope equipped with 4K quality vision track,
- Technical specifications:
 - Infinitely adjustable light intensity,
 - Fiber optic,
 - Magnification adjustment: 0.4x / 0.6x / 1x / 1.6x / 2.5x,
 - Eyepiece: 10x,
 - Focal length (f): 300,
 - Switchable to green filter,
 - Infinitely adjustable:
 - Eyepiece height from 92 - 136 cm,
 - Infinitely adjustable microscope and side-to-side arm,
 - Camera apertures,
 - Image sharpness,
 - Eyepiece spacing in the range: 20 mm,
 - There are knobs on the pantographic arm to lock it in the selected position,
- Colposcope expanded with 4K video track which includes:
 - DELL 4K monitor:
 - Screen diagonal: 23.8",
 - Matrix: LED - IPS,
 - Screen resolution: 3840 x 2160 (UHD 4K),
 - Aspect ratio: 16:9,
 - Image frequency: 60 Hz,
 - Connectors: HDMI/MHL / DisplayPort / Mini DisplayPort / USB 3.2 (4 pcs.), USB-B 3.2 (1 pc.),
 - SONY CMOS 4K Camera:
 - Sensor: Sony 1/2.8-inch CMOS sensor with 8.29 million pixels,
 - Pixel size: 1.45 µm x 1.45 µm,
 - HDMI Output: 3840x2160 at 30 frames/1920x1080 at 60 frames,
 - USB output: 3840x2160 / 2560x1440 / 1920x1080 / 1280x720 / 640x480 / 424x240 / 320x240 (MJPEG format),
 - Lens interface: C/CS,
 - Exposure: Automatic/Manual,
 - Exposure Compensation: Supported,
 - White Balance: Automatic/Manual, R, G, B adjustment supported,
 - Memory: Supports up to 64 GB,
- Unit on mobile 5-wheel base (2 brake wheels),
- Included:
 - Power cords,
 - 64 GB memory card + adapter (microSD / microSDHC / microSDXC),
 - Remote control for camera functions,
- Overall dimensions: 70 x 80 x 150 cm,
- Weight: 60 KG,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
 - The warranty period does not include bulbs and other light sources installed in the device,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

