



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **KETTLER UNIX PX Magnetic crosstrainer (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- KETTLER UNIX PX features motor-controlled resistance control and precision technology. In addition, the UNIX PX offers exercisers the well-known and proven EXT technology and enables even more effective training of all body parts,
- HeartRateLight will take care of ensuring that your heart rate stays within a safe range. If your heart rate rises too high, the display color will turn red, and if your heart rate is too low, it will turn blue,
- Technical specifications:
  - LCD display (3-color backlight),
  - Continuous display: 8 functions,
  - Graphic display: load profile + HeartRateLight function,
  - Braking system: motor-controlled magnet,
  - Drive system: drive disc / belt with longitudinal ribbing,
  - Freely scaled performance programs: 6,
  - Upper heart rate limit: percentage display and visual and audible warning signal,
  - Number of workout programs: 8,
  - Measurements: time / training distance / total distance / speed / cadence / heart rate measurement,
- Features:
  - Resting heart rate measurement with fitness assessment,
  - Heart rate controlled workout program,
  - Manual load control,
  - Parameter control,
  - Target zone training: FAT / FIT / MANUELL,
  - Displayed average values at the end of the workout,
- Included:
  - Power cord,
  - Clip on lugs to detach from
  - Clip on ear for heart rate reading,
- Dimensions: 56 x 144 x 162 cm,
- Maximum load capacity: 150 KG,
- Weight: 67 KG,
- Has up-to-date inspection and is ready for use,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

