



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



RIGHTON SPEEDY-K2 Autorefractometer with keratometer (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Japan, (2016),
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 40 VA,
- The measurement principle of the Speedy series enables extremely fast, automatic measurement of refraction and keratometry. This technology was originally developed by NIKON for the world's first Speedy series,
- Accommodative control during the test completed with a printout of the resting accommodative value,
- Measurement of residual astigmatism necessary for contact lens and IOL calculations,
- Special measurement mode for children and people with nystagmus,
- Measurement reliability indicator,
- Technical specifications:
 - Refraction measurement:
 - Measurement range:
 - Sphere (D) measurement range: -20D to +23D,
 - Cylinder measurement range (D): 0D to +/- 12D,
 - Axis: 0° from 0° to 180° (adjustable in 1° increments),
 - Minimum pupil diameter: 2.3mm,
 - Corneal astigmatism; +/-12 D,
 - PD measurement: 1 to 83 mm,
 - Pupil size reading range: 2.0 to 12.0 mm,
 - Apex distance: 0 / 12 / 13.5 / 13.75 / 15 / 16 mm,
 - Keratometry measurement:
 - Measurement range:
 - Corneal curve: 5.00 to 11.00 mm,
 - Corneal astigmatism: 0.00D to 12.00D,
 - Axis: From 0° to 180°,
 - Measuring area:
 - Central: ø3.2 mm,
 - Outer: 25° - ø6.8 mm,
 - Corneal size measurement range: 0 to 16.00 mm,
 - Memory capacity: 50 people (100 pairs of eyes),
 - Touch screen display: 5.7 inch LCD,
 - Built-in thermal printer with a paper width of 6 cm,
 - Interface:
 - US232C,
 - USB,
 - IR,
- English language menu,
- Included:
 - Power cord,
- Dimensions:
 - Overall: 25 x 46 x 44 cm,
- Weight: 13 kg,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

