



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Slit lamp (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Bulb: 12 V / 50 W,
- Technical specifications:
 - Magnification eyepiece: 15x,
 - Dioptic adjustment: +/- 8D,
 - Aperture length: 12 mm (1 - 12 mm continuous variable),
 - Aperture dimensions: 0.2 / 1 mm square / 2 / 3 / 5 / 9 / 12 mm,
 - Aperture angle: +/- 90°,
 - Slit rotation: +/- 180° with reference scale,
 - Magnification switch: 1x / 1.6x,
 - Free adjustment of eyepiece spacing,
 - Free adjustment of light source intensity,
- Built-in filters:
 - Blue,
 - Yellow,
 - Green,
 - Neutral,
- Built-in fixation point,
- Manual chin height adjustment within 7 cm,
- Slit lamp placed on a mobile 4-wheel table (2 braking wheels) TOPCON IT-1:
 - Manual height adjustment of the table within 24 cm,
- Included:
 - Power cord,
- Overall dimensions: 54 x 40 x 135/159 cm,
- Weight: 30 KG,
- Has a current inspection and is ready for use,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

