



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



MEIKO TOPLINE 40 Duck and pool washer (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 400 V,
- Frequency: 50/60 Hz,
- Power: 4.6 kw 16A,
- MEIKO TOPLINE is used for emptying, washing and disinfection of ducks, pools and kidney dishes,
- All made of stainless steel,
- Technical specifications:
 - Four operation programs,
 - System water pressure: 1 Bar,
 - Boiler capacity: 2.1 L,
 - Water pressure: 100-500 kPa,
 - Noise level: 50 db,
 - Washing water temperature: 45-60 °C,
 - 13 nozzles including; 1 telescopic, rotary nozzle, 3 duck nozzles, 3 upper, 2 middle and 3 lower rotary nozzles and 1 nozzle for washing dishes from outside,
 - Cycle times:
 - Short program: 4-5 min,
 - Normal program: 5-6 min,
 - Intensive program: 6.5-7 min,
 - (Additional cycles can be modified and individually set),
- Keypad on control panel in language: EN, DE,
- Included:
 - User manual in English (PDF),
 - Power cord with 400 V power plug,
 - Cold and hot water supply hose,
- Dimensions: 140 x 60 x 90 cm,
- Weight: 95 kg,
- Cat 01,
- It has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

