



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



YZ5FI Slit lamp (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Bulb: 12 V / 30 W,
- Technical specifications:
 - Magnification eyepiece: 12.5x,
 - Dioptic adjustment: +3 / -5D,
 - Magnification: 6x / 10x / 16x / 40x / 25x,
 - Built-in fixation point,
 - Maximum chin height adjustment in range: 25 - 32 cm,
 - Free adjustment of eyepiece spacing,
 - Slit rotation in the range of 180°,
 - Built-in filters:
 - Blue,
 - Green,
 - Neutral,
 - Cobalt,
 - Amber,
- Slit lamp placed on MDT table:
 - Height adjustable from: 73 - 93 cm,
 - 3 degree adjustment of light source intensity,
- Included:
 - Power cord,
 - Applanation tonometer,
- One of the eyepieces has a slight damage that does not interfere with the comfort of use,
- Overall dimensions: 45 x 66 x 143 cm,
- Weight: 38 KG,
- It has a current inspection and is ready for use,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
 - The warranty period does not include bulbs and other light sources installed in the device,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

