



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



MELAG Vacuclave 550 Autoclave (New)

- New,
 - Made in Germany,
 - New autoclave opens up new possibilities - more sterilized instruments in less time. Swap two autoclaves for one. The MELAG Vacuclave 550 provides significantly more capacity with 40% less space compared to two alternative small autoclaves,
 - Sterilize the maximum number of instruments in the minimum space in record time. With an extra-large chamber and unprecedented innovations with the Vacuclave 550, you'll be ready for anything: discover the advantages of our new 50-liter autoclave that saves energy, time and money,
 - Features and benefits of the MELAG Vacuclave 550 autoclave:
 - Exceptional capacity: More space for loading up to 25 kg on 16 trays or in 10 MELAstore boxes,
 - Impressive speed: Patented pressure jacketed chamber technology for record-breaking run times,
 - Intelligent drying: Reduce drying time with DRYtelligence by up to 80%,
 - Uncompromising comfort: Extra-large Polish-language Smart-Touch display for intuitive operation as simple as a smartphone,
 - Traceable documentation: Documentation and release directly from the screen thanks to ProControl,
 - Pioneering technologies: Recovery, Coolify, Power Save and DRYtelligence make the Vacuclave 550 the cleanest solution - for your budget and the environment,
 - Vacuclave 550 proves true greatness: the new 50-liter autoclave combines environmental protection with economy. Thanks to pioneering solutions, it saves electricity, water and therefore money with every sterilization cycle*. ✓ More power, less energy: The four technologies outlined above allow the efficient Vacuclave 550 to save about €2,200 worth of energy*,
 - Saving water also means saving money: The Vacuclave 550 saves 1,300,000 liters of water over its lifetime compared to units with a hydraulic connection,
 - Because fewer units mean lower costs: The service-friendly appliance concept cuts maintenance and repair costs in half,
 - Technical specifications:
 - Chamber size: D 45 cm x Ø 38 cm,
 - Chamber volume: 53 l,
 - Appliance dimensions (W x H x D): 63.6 x 59 x 71.5 cm,
 - Loading size:
 - 15 amp: 25 kg unpacked, 11 kg packed, 3.5 kg textiles,
 - 13 amp: 17.5 kg unpacked, 9 kg packed, 2 kg textiles,
 - Height with display: 65 cm.
 - Requires a countertop with a depth of 60 cm.
 - Weight: 98 kg,
 - Power supply: 220-230 V/50-60 Hz,
 - Power consumption:
 - 15 amp: 3 400 W,
 - 13 amp: 2 700 W,
 - Documentation interfaces: USB, network,
 - Has a current Technical Passport issued,
 - Warranty 12 months,
 - Financing options (Poland only): Installments, Leasing, Loan,
- If you have any questions, please do not hesitate to contact us!
- In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

