



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



MELAG Vacuclave 550 Autoclave (New)

- New,
 - Made in Germany,
 - New autoclave opens up new possibilities - more sterilized instruments in less time. Swap two autoclaves for one. The MELAG Vacuclave 550 provides significantly more capacity with 40% less space compared to two alternative small autoclaves,
 - Sterilize the maximum number of instruments in the minimum space in record time. With an extra-large chamber and unprecedented innovations with the Vacuclave 550, you'll be ready for anything: discover the advantages of our new 50-liter autoclave that saves energy, time and money,
 - Features and benefits of the MELAG Vacuclave 550 autoclave:
 - Exceptional capacity: More space for loading up to 25 kg on 16 trays or in 10 MELAstore boxes,
 - Impressive speed: Patented pressure jacketed chamber technology for record-breaking run times,
 - Intelligent drying: Reduce drying time with DRYtelligence by up to 80%,
 - Uncompromising comfort: Extra-large Polish-language Smart-Touch display for intuitive operation as simple as a smartphone,
 - Traceable documentation: Documentation and release directly from the screen thanks to ProControl,
 - Pioneering technologies: Recovery, Coolify, Power Save and DRYtelligence make the Vacuclave 550 the cleanest solution - for your budget and the environment,
 - Vacuclave 550 proves true greatness: the new 50-liter autoclave combines environmental protection with economy. Thanks to pioneering solutions, it saves electricity, water and therefore money with every sterilization cycle:*. ✓ More power, less energy: The four technologies outlined above allow the efficient Vacuclave 550 to save about €2,200 worth of energy*,
 - Saving water also means saving money: The Vacuclave 550 saves 1,300,000 liters of water over its lifetime compared to units with a hydraulic connection,
 - Because fewer units mean lower costs: The service-friendly appliance concept cuts maintenance and repair costs in half,
 - Technical specifications:
 - Chamber size: D 45 cm x Ø 38 cm,
 - Chamber volume: 53 l,
 - Appliance dimensions (W x H x D): 63.6 x 59 x 71.5 cm,
 - Loading size:
 - 15 amp: 25 kg unpacked, 11 kg packed, 3.5 kg textiles,
 - 13 amp: 17.5 kg unpacked, 9 kg packed, 2 kg textiles,
 - Height with display: 65 cm.
 - Requires a countertop with a depth of 60 cm.
 - Weight: 98 kg,
 - Power supply: 220-230 V/50-60 Hz,
 - Power consumption:
 - 15 amp: 3 400 W,
 - 13 amp: 2 700 W,
 - Documentation interfaces: USB, network,
 - Has a current Technical Passport issued,
 - Warranty 12 months,
 - Financing options (Poland only): Installments, Leasing, Loan,
- If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

