



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



MELAG Pro Line Vacuclave 123 Autoclave (New)

- New,
- Made in Germany,
- The MELAG Pro Line Vacuclave 123 autoclave is a freestanding model with the ability to connect to a water treatment system,
- From loading to sterilization to documentation, the compact Class B autoclave offers a favorable price/performance ratio that is second to none. With ProLine autoclaves, you'll sterilize more instruments in less time, which translates directly into financial savings. And all these advantages come at the highest MELAG quality,
- ProLine series models offer everything you need for safe, friendly and resource-saving sterilization,
- Features and advantages of the MELAG Pro Line Vacuclave 123 autoclave:
 - Powerful Class B vacuum: Reliably sterilizes up to 6 kg of instruments in 5 trays in 16 - 28 minutes (plus drying),
 - Smart - Touch display with LED status: Touchscreen display with intuitive user interface for easy smartphone-like operation, even with protective gloves,
 - Connectivity and data logging: Legally compliant recording of sterilization data on a USB flash drive or via a network connection,
 - Freestanding autoclave concept: Integrated water tanks and efficient air cooling for cooling water independent operation,
 - Power - Save mode: Heater and display go to sleep between operation cycles for energy efficiency,
 - Easy - Care concept for easy routine maintenance: User-friendly optimization for efficient filter replacement, tank cleaning and water supply,
- Technical data:
 - Class B autoclave,
 - Chamber size: G 45 cm x Ø 25 cm,
 - Chamber volume: 23 l,
 - Device dimensions (W x H x D): 47 x 50 x 64 cm,
 - Loading size: 6 kg of instruments, 2 kg of textiles,
 - Requires a countertop with a minimum depth of 60 cm,
 - Weight: 49 kg,
 - Power supply: 220-230 V/50-60 Hz,
 - Power consumption: 2100 W,
 - Documentation interfaces: USB, Network,
- Has a current Technical Passport issued,
- Warranty 12 months,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

