



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



YESON Steel + Water Distiller (New)

- New,
- The STEEL+ distiller is the latest version of the STEEL distiller appreciated by demanding users,
- The STEEL + distiller has been equipped with a number of facilities that improve the comfort of use along with the reliability known from the previous model. The entire water circuit (tank, interior of the head, coil, filter housing) is made of high quality stainless steel, the external appearance of the device has been modified.
- The distilled water container is made of an aesthetic and durable material with high transparency. The new, damage-resistant container lid increases the convenience of use and properly protects the distilled water from contamination during storage,
- The appropriate thickness of the walls of the tank in which the water is heated affects the long-term durability of the distiller,
- The distiller has a fuse in the socket on the distiller housing and an additional switch that allows you to easily turn the distiller on and off,
- The vandal-resistant filter housing is made of polished stainless steel,
- New tank heater with increased durability and 800 W power,
- Aluminum fan ensuring adequate cooling performance,
- **Application:**
 - To produce distilled water of higher quality than chemically demineralized water, to ensure reliable operation of various devices,
 - Irreplaceable in dental offices, laboratories, car workshops, restaurants, hotels, bars,
- **The obtained water is distilled to:**
 - Autoclaves and dental units,
 - Air humidifiers,
 - Dilution of alcohol and other liquids,
 - Refilling fluids in acid batteries,
 - In espresso machines (preparing hot drinks),
- **Standard equipment:**
 - Distillery,
 - Water tank with connector and filter,
 - Power cord,
 - Cleaning powder,
 - User manual in Polish,
- **Technical data:**
 - Power supply 230V (220-240V),
 - Power consumption 800W,
 - Water tank capacity 4 liters,
 - Efficiency - approx. 1 liter per hour,
 - Dimensions: height 38 cm / diameter 24 cm,
 - Weight: 6 kg,
- Has a valid Technical Passport issued,
- 12 month warranty,

