



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



YESON SMART + (New)

- New,
- **Features and advantages of the welding machine:**
 - A very elegant, energy-saving welder equipped with an electronically controlled heating element,
 - A modern device that helps prepare paper-foil packages for sterilizing tools in an autoclave,
 - Sterilization in packages is considered to be a particularly effective, safe and convenient method,
 - It allows you to store sterile tools for a longer period of time after the process has been carried out,
 - The sealer can be used to close ready-made packages or sleeves in rolls of various widths,
 - A knife with a double-sided blade allows precise cutting of the required section of the sleeve,
 - Automatic temperature control of the heating element helps to obtain very good quality welds,
 - Device status indicated by a diode,
 - Energy saving function - automatic switch to standby mode during a break in work,
- **Technical data:**
 - Voltage 230V / 50Hz,
 - Power 500W,
 - Maximum weld length 300 mm,
 - Seam width 12 mm,
 - Device weight 8.8 kg,
 - Dimensions: 517 x 283 x 205 mm,
- Has a valid Technical Passport issued,
- 12 month warranty,

