



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Muffle furnace CZYLOK FCF 2.5P (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Poland,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Power: 0.9 kW,
- Muffle furnaces are designed to carry out thermal processes in laboratories with particular application in conditions of occurrence of aggressive environment in the chamber in the form of gases, dusts, splatters, etc.,
- Ceramic muffle, separates heating elements from the inside of the heating chamber and ensures longer life and stable temperature maintenance,
- One four-character display makes it easy to read the actual temperature of the object and the set parameters. With the ability to program a delayed start time as well as an annealing time, i.e. maintaining the temperature of the furnace for a specified period of time, it is possible to automatically carry out an unattended firing cycle,
- Temperature control in the range: 20 - 1150°C
- Operating temperature: 1100°C,
- Warm-up time up to 1000°C - 50 minutes,
- Included:
 - Power cord,
- Dimensions:
 - Overall: 50 x 52 x 36 cm,
 - Working chamber: 14 x 18 x 10 cm,
- Weight: 25 KG,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

