



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



OLYMPUS OEP-4 HDTV Printer (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- **Real photos of the product,**
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- **Technical specifications:**
 - Dedicated printer paper: UPC-55,
 - Resolution: 379 DPI,
 - Print speed: 29 seconds,
 - Number of prints: 1 to 10 copies,
 - **Input signal:**
 - HDTV signal (1080/59.94i) - RGB video/YPbPr signal,
 - Y/C video signals,
 - Composite video signal,
 - **RGB video (HDTV) signals:**
 - 0 to 0.7 Vp-p (video) ± 0 ,
 - 3 Vp-p (sync),
 - **RGB video signals:**
 - 0 to 0.785 Vp-p,
 - **Composite sync:**
 - 1.0 to 4.0 Vp-p,
 - **Y/C video signals:**
 - 0 to 0.714 Vp-p,
 - **Composite video:**
 - 0 to 0.714 Vp-p,
 - **Output signal:**
 - **RGB video (HDTV) signals:**
 - 0 to 0.7 Vp-p (video) ± 0 ,
 - 3 Vp-p (sync),
 - **RGB video signals:**
 - 0 to 0.785 Vp-p,
 - **Composite sync:**
 - 4.0 ± 0.5 Vp-p,
- **Included:**
 - English user manual (PDF),
 - Power cord,
- Dimensions: 28 x 40 x 12.5 cm,
- Weight: 9 KG,
- **Has an up-to-date inspection and is ready for operation,**
- **Issued Technical Passport (Service Report) valid for a period of 12 months,**
- **Warranty:**
 - **6-months for domestic market (Poland),**
 - **3-months for the international market,**
 - **Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,**
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

