



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



SONY UP-897MD Videoprinter (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Technical specifications:
 - Thermal printing,
 - 256 shades of gray,
 - High print resolution:
 - EIA: 1210 x 490 pixels,
 - CCIR: 1210 x 582 pixels,
 - Print speed: ~2 seconds,
 - VIDEO input and output,
- When the print button is pressed, the UP-897MD can capture and store up to 10 uploaded images in its built-in memory. The images stored in memory can be viewed on an optional monitor and selected and printed using the corresponding menu option,
- Users can also scale image data in selected areas before reprinting,
- English language menu,
- Included:
 - User manual in ENG, FR, GER, ESP, IT, JP(PDF),
 - Power cord,
- Dimensions: 15 x 24 x 9 cm,
- Weight: 2.6 KG,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
 - The warranty period does not include bulbs and other light sources installed in the device,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

