



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



SONY DVO - 1000MD DVD writer (Reconditioned)

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Japan,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- Sony recorder is a small, durable and easy to use digital data archiving device,
- Product features:
 - Enables video recording and playback in a wide range of visible light and other modes,
 - Hard drive provides additional protection for recordings in case of power loss,
 - Can record up to 3 h on a single disc,
 - Recording on DVD-RW discs,
 - DVOFAST function allows the operator to eject the disc in less than 2 minutes after recording without finalizing the disc,
 - Freeze mode allows the operator to set a frame or field as the first image,
 - Convenience of browsing through recordings thanks to an automatically created list displayed by pressing the LIST button on the front of the unit,
 - RS - 232C connector allows remote control with other devices and video playback at 30-ct speed,
 - Option to switch between PAL and NTSC from the menu,
 - Keypad on the control panel and menu in English,
- Specifications:
 - Recording modes:
 - HQ mode: 60 min,
 - SP mode: 120 min,
 - LP mode: 180 min,
 - Recording format:
 - Video: MPEG - 2,
 - Audio: Dolby Digital,
 - Recording medium: DVD + RW,
 - Media recording speed: 2.4 x, 4 x,
- Equipped with various kinds of inputs and outputs:
 - Analog VIDEO inputs and outputs:
 - VIDEO IN - OUT: 3 BNC sockets (including 2 for VIDEO IN),
 - S-VIDEO IN - OUT: 3 4-pin DIN sockets (including 2 for S - VIDEO IN),
 - AUDIO analog inputs and outputs:
 - AUDIO IN - OUT: 4 jack sockets for right and left channels,
 - AUDIO MONITOR: 1 jack socket,
 - PILOT 1: stereo mini jack socket for SVRM - 100A remote control (no remote control included),
 - PILOT 2: mini jack socket for foot switch (no switch included),
 - Digital signal socket and LINK (DV IN),
 - RS - 232C socket,
 - USB 2.0 socket,
- Included:
 - User manual in English (PDF),
 - Power cord,
- Dimensions: 21.5 x 13 x 39 cm,
- Weight: 6 KG,
- Cat 04,
- Has a current inspection and is ready for operation,
- Issued Technical Passport (Service Report) valid for 12 months,
- Warranty:
 - 6-months for domestic market (Poland),
 - 3-months for the international market,
 - Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
- Financing options (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

