



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **KARL STORZ TELECAM DXII Camera processor with KARL STORZ HALOGEN 250 TWIN light source (Reconditioned)**

- Reconditioned (used),
- Technical condition: very good,
- Visual condition: very good,
- Real photos of the product,
- Made in Germany,
- Power supply: 230 V,
- Frequency: 50/60 Hz,
- KARL STORZ TELECAM DXII processor:
  - PAL / NTSC color system,
  - Electronic froscope filter,
  - Features jacks:
    - 2 x S-Video (Y/C),
    - 2 x Stereo 3.5 mm (jack),
    - BNC,
  - Processor equipped with STORZ TELECAM 20212030 PAL camera,
- KARL STORZ HALOGEN 250 TWIN light source:
- The Storz 250 TWIN is a halogen light source suitable for flexible endoscopes,
- Technical specifications:
  - Halogen light,
  - 2 24 V 250 W incandescent lamps,
  - Color temperature: 3000 K,
  - 3-stage adjustment of light intensity with a knob,
  - Bulbs protected by an additional cover,
  - Manual selection of the bulb to work with the included allen key hidden under the cover of the device,
  - Input for the other end of the fiber optic cable protects against damage during a break in operation,
  - Screw-out fiber optic input allows its installation of an adapter corresponding to another manufacturer's fiber optics (adapter not included),
  - Foiled control panel,
- Included:
  - Power cord,
  - STORZ TELECAM processor camera 20212030 PAL,
  - S-VIDEO cable,
- Dimensions:
  - KARL STORZ TELECAM Processor DXII: 30.5 x 24.5 x 8.5 cm,
  - KARL STORZ HALOGEN 250 TWIN light source: 30.5 x 24.5 x 11 cm,
- Total weight: 10 KG,
- It has a current inspection and is ready for use,
- Issued Technical Passport (Service Report) valid for a period of 12 months,
- Warranty:
  - 6-months for domestic market (Poland),
  - 3-months for the international market,
  - Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
  - The warranty period does not include bulbs and other light sources installed in the device,
- Possibility of financing (Poland only): Installments, Leasing, Loan,

If you have any questions, please do not hesitate to contact us!

In case you don't find the product you are interested in, please get in touch with us and we will do our best to find the perfect solution for YOU.

