



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



OLYMPUS OCS-2 colposcope (video track) (Reconditioned)

- o Reconditioned (used),
- o Technical condition: very good,
- o Visual condition: very good,
- o Real product photos,
- o Japanese production,
- o Power supply: 230 V,
- o Frequency: 50/60 Hz,
- o Light source: 50 W LED bulb,
- o Technical specifications:
 - Eyepiece: 20x,
 - Magnification: From 7x to 20x,
 - Adjustable eyepiece spacing,
 - Built-in filter:
 - Green,
 - Neutral,
 - Freely adjustable 43 cm arm,
 - Eyepiece height adjustment within 25 cm,
- o Colposcope equipped with a vision path:
 - New AmScope light source:
 - Power supply 230 V,
 - 50W LED bulb,
 - Smooth adjustment of light intensity,
 - Monitor SAMSUNG:
 - Screen size: 24",
 - Resolution: 1920 x 1080,
 - Matrix: LCD,
 - Response time: 5 ms,
 - Brightness: 300 cd/m²,
 - CANON EOS M3 camera:
 - Equipped with a 22.3 x 14.9 mm CMOS matrix with a resolution of 24.2 MP,
 - Large, bright touch screen provides a clear image,
 - Simple function control and excellent work in low light enable recording of high quality images,
 - Image processor: DIGIC 6,
 - Focus adjustment: Hybrid CMOS AF II,
 - ISO sensitivity: 100 - 12800,
 - Automatic white balance set by the matrix,
 - 3" sRGB Clear View LCD II touch screen,
 - Aspect ratio 3:2,
 - Possibility to select menu in: PL, EN, DE, FR, ES, RU, PT, CS, IT, FI, NL, SV, NO, HU, DA, TR, RO, AR,
 - Support for SD, SDHC, SDXC cards,
 - Video: Full HD, 30 frames/s,
 - Images: RAW, JPEG,
- o Mobile on a 5-arm base with wheels - 3 wheels with brakes,
- o Included:
 - Power cable,
 - Fiber optic cable,
 - 8GB micro SD card with adapter,
 - Wi-Fi card,
 - Charging station with CANON battery,
 - Charging station with Newell battery,
- o Dimensions:
 - 61 x 135 cm,
- o Weight: 56 KG,
- o Has a current inspection and is ready to work,
- o Issued Technical Passport (Service Report) valid for 12 months,
- o Warranty:
 - 6 months for the domestic market (Poland),
 - 3 months for the international market,
 - Possibility of extending the warranty for an additional fee to 12 months for the domestic and international market,
- o Financing options (Poland only): Installments, Leasing, Loan,

