



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



SCITON JOULE laser (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Manufactured by U.S.A., (2013),
Power supply: 230 V,
Frequency: 50/60 Hz,
JOULE™ is an aesthetic system based on the action of light and a laser beam that combines everything you need in one personalized platform,
Innovative approach, focus on results and reliability are the values that are the foundations of Sciton technology, on which the JOULE™
concept was based,
Application:
Uneven skin tone,
Acne and acne scars,
Fine lines and wrinkles,
Scars,
Brown spots,
Skin flabbiness,
Unwanted hair,
Sciton Joule laser treatments with Halo-BBL effect:
Laser micropeeling,
Deep skin peeling for wrinkle reduction,
Fractional laser skin resurfacing,
Removal of sun spots and age spots,
Acne scar reduction and acne treatment,
Skin firming,
Laser hair removal,
Blood vessel treatment,
Smart filters and different wavelengths:
420 nm - Acne,
515 nm - Pigmentary lesions such as freckles, age spots,
560 nm - Vascular lesions such as cherry angiomas, telangiectasias and rosacea,
590 nm - Deeper lesions / Darker skin types,
590 nm, 640 nm and 695 nm - Hair removal,
Selectable menu in language: English,
Included:
SCITION 1500-202-20 handpiece,
Adapter:
SCITION 1500-202-52,
SCITION 1500-202-53,
SCITION 1500-202-54,
Glass filter:
1x 695,
1x 640,
1x 590,
1x 560,
1x 515,
1x 420,
SCITION 1500-010-17 handle,
SCITION 1500-500-43 Handpiece,
Handle 2 mm 2.94μ / 3 mm 755 nm / 1.06 μ,
Handle 4 mm 2.94μ / 6 mm/1.06μ,
5 x spacer,
5 x safety glasses,
Sterilization container,
Power cord,
Overall dimensions: 52 x 77 x 182 cm,
Weight: 70 KG,
Has a current inspection and is ready for operation,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
Financing options (Poland only): Installments, Leasing, Loan,

