



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Polometer (perimeter) CARL ZEISS HUMPHREY SYSTEM 740i (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Manufactured by U.S.A.,
Power supply: 230 V,
Frequency: 50/60 Hz,
Halogen lamp: 12 V / 30 W,
Humphrey 740i
is the entry-level model of Zeiss automatic visual field perimeter measurement, which provides comprehensive care in the diagnosis and treatment of glaucoma,
Enhanced Guided Progression Analysis (GPA) software - automatically identifies statistically significant progression,
Visual Field Index (VFI) - an intuitive new global index for determining percent field loss,
Pattern Deviation Charts - identifies local visual field loss, minimizing the effects of ocular media such as cataracts,
STATPAC - compares results with proprietary age and glaucoma normative databases,
Kinetic, Custom and Social Security tests provide a wide range of special-purpose testing protocols,
HFA-NET Pro with EasyConnect RCT - provides plug-n-play connectivity solutions that improve office efficiency,
DICOM gateway option supports connectivity,
Touchscreen and menu-driven interface for simple operation,
Ergonomic design for maximum comfort and versatility,
Network capabilities,
Customized printing,
Device equipped with LEXMARK printer with paper roll diameter: 22 cm,
Polometer placed on CARL ZEISS mobile table (4 wheels with brake) with electric height adjustment in the range: 68 - 95 cm,
Selectable menu in language: ENG, GER, ESP, FR, IT, JP, PT, SWE,
Includes:
User manual in English (PDF),
Power cord,
Keypad,
Patient button,
LEXMARK printer,
CARL ZEISS mobile table,
Dimensions:
General: 100 x 60 x 180 cm,
Weight: 55 KG,
Has a current inspection and is ready for use,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

