



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



INAMI Slit Lamp L-0185 (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Japanese production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Halogen bulb: 12 V / 50 W,
Technical Dante:
Microscope:
Magnification eyepiece: 16x,
Convergence angle: 13°,
2 degree magnification,
Pupil spacing: 52 - 90 mm,
Focal distance: 100 mm,
Dioptric adjustment: +8 / -8 D,
Slit illumination:
Slit width: 0 - 10 mm,
Slit length: 0 - 10 mm,
Slit diameters: 0.2 / 1 / 3 / 4 / 6 / 10 mm.,
Slot rotation: +/- 90°,
Slot tilt: 5° / 10° / 15° / 20°,
Fixation lamp: LED,
Light source: HALOGEN 12 V / 50 W,
Maximum light intensity: 350,000 Lux,
Free adjustment of light intensity with a knob,
Built-in filters:
Cobalt blue,
Heat absorption filter,
Red-free filter,
½ ND built-in yellow filter in the eyepiece,
Slit lamp equipped with an electric OPTOPOL table:
Electrically adjustable in height from 67 - 93 cm,
Included:
Power cord,
OPTOPOL electric table,
Dimensions:
Lamps: 55 x 40 x 66 cm
Total: 62 x 46 x 136/161 cm,
Weight:
Lamps: 18.5 KG,
Total: 45 KG,
It has a current inspection and is ready for operation,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

