



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



OLYMPUS VISERA CLV-S40 light source (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Japanese production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Xenon light,
Foiled control panel,
Bulbs:
Xenon MD-631 of 300 W - main lighting,
Halogen 150 W - emergency lighting,
Features:
WHITE BALANCE function - Automatic white balance,
+/- 8 degrees of light intensity adjustment,
Features "freeze" function,
Included:
User manual in English (PDF),
Power cord,
Dimensions: 37 x 41 x 14 cm,
Weight: 11.8 KG,
Has an up-to-date inspection and is ready for use,
Issued Technical Passport (Service Report) valid for a period of 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,
The warranty period does not include bulbs and other light sources installed in the device,
Possibility of financing (Poland only): Installments, Leasing, Loan,

