



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



ALFA-ELECTRONICS cross-over camera (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Polish production, (2017),
Power supply: 230 V,
Frequency: 50/60 Hz,
Apparatus intended for testing:
Drivers,
Candidates for drivers,
Instructors,
Examiners,
Candidates for instructors, examiners,
Employees in positions requiring specific psychophysical fitness (forklifts, excavators, overhead cranes, cranes, etc.),
Other examinees in the field of transport psychology and occupational medicine,
Equipped with:
Measuring electronics,
Easy-to-read LCD display,
Ergonomic control module that comes with the apparatus,
The apparatus allows testing in the range of:
Imposed pace : 30, 50, 70, 90 stimuli / minute,
Free tempo with a test time of 30 / 60 / 120 seconds or 49 / 73 / 98 stimuli,
The apparatus automatically calculates and presents on the display:
Test duration,
Number of stimuli presented,
Number of accurate (correct) responses,
Number of incorrect responses,
No response (number of stimuli missed),
Average reaction time,
Median reaction times,
Minimum reaction time,
Maximum reaction time,
Included:
Power adapter,
Dimensions: 33 x 40 x 22 cm,
Weight: 4 KG,
Has an up-to-date inspection and is ready for operation,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
Financing options (Poland only): Installments, Leasing, Loan,

