



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



ASM-ELECTRIC ASMEDI electric wheelchair (Ex-Display)

New (post-show),

Real photos of the product,

Polish production, (2024),

Emergency power supply: through 1 new built-in 24 V / 12 Ah battery,

Frequency: 50/60 Hz,

ASM Electric

is an electric wheelchair that has an efficient motor with a range of up to 20 km on a single charge. It performs perfectly both indoors and outdoors,

Its small size and easy folding and unfolding makes it easy to move around. The control panel has an on-off button, illuminated buttons, universal joystick, horn,

The cart is equipped with a safe and non-waterproof electronic brake and a lead-acid battery. The anti-rollover system makes moving on this cart completely safe,

Each component provides high quality, convenience and safety making the product an ideal choice for those seeking comfort and reliability, Features:

Each component provides high quality, convenience and safety making the product an ideal choice for those seeking comfort and reliability,

Foldable frame and backrest make it easy to transport and store, saving space,

PU padded armrest is durable and easy to clean,

Airy and durable seat and backrest cushion increases comfort,

Airy oxford fabric base with mesh fabric ensures thermal comfort, providing adequate air circulation,

Seat belt provides a high level of safety,

Swiveling armrests allow comfortable transfer from the wheelchair to the bed,

Foldable footrests with calf strap provide comfortable leg support and easy storage when folded,

Specifications:

Universal rocker controller allows you to conveniently adjust the position of the unit, with left and right sides interchangeable,

High-speed 250W motor 2 fast and efficient operation of the device for efficient operation,

Electronic brake ensures precise speed control and safe use,

Power and manual mode gives you the ability to adjust the operation mode according to your needs,

Range: 20 km $\pm 10\%$ * provides sufficient range for daily use,

Maximum speed: 6km/h allows comfortable driving in various conditions,

Front wheel: 8-inch solid PU tire and Rear wheel: 12-inch pneumatic tire guarantee durability and ride comfort,

Lead-acid battery (24 V / 12 Ah) ensures long-lasting operation on a single charge, reducing the frequency of recharging,

Includes:

User manual in Polish,

Power adapter with power cord,

Dimensions:

Overall: 63 x 98 x 91.5 cm,

Seat: 44 x 43 cm,

Maximum load capacity: 100 KG,

Weight: 30 KG,

Has a current inspection and is ready for use,

Issued Technical Passport (Service Report) valid for 12 months,

Warranty:

6-months for domestic market (Poland),

3-months for the international market,

Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,

Financing options (Poland only): Installments, Leasing, Loan,

