



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **CARL ZEISS HSO-10 handheld slit lamp (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Bulb: OSRAM 6 V / 10 W,  
Slit lamp  
CARL ZEISS HSO-10  
is used to examine the anterior and posterior segments of the eye,  
The lamp has an arc guide for free movement of the eyepiece,  
Technical specifications:  
Focal length (f): 125,  
Dioptric adjustment +/- 3 D,  
Eyepiece spacing: 55 - 75 (20 mm.),  
Built-in filters:  
Neutral,  
Blue,  
Green,  
Adjustable light shape settings:  
Circular,  
Post-shaped light beam in two widths,  
Free adjustment of light beam size,  
Free 9-step adjustment of light intensity,  
Included:  
Power cord,  
Power supply,  
Dedicated carrying case,  
2 pcs case key,  
Spare 6 V/ 10 W bulb,  
Weight: 1.25 KG,  
Has a current inspection and is ready for operation,  
Issued Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,  
Financing options (Poland only): Installments, Leasing, Loan,

