



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



CARL ZEISS HUMPHREY SYSTEM 740i Fieldmeter (perimeter) (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real product photos,
Manufactured in the U.S.A.,
Power supply: 230 V,
Frequency: 50/60 Hz,
Halogen lamp: 12 V / 30 W,
Humphrey 740i is the basic model of automatic measurement of the perimeter of the visual field from Zeiss, which provides comprehensive care in the diagnosis and treatment of glaucoma,
Main features:
Enhanced Guided Progression Analysis (GPA) software - automatically identifies statistically significant progression,
Visual Field Index (VFI) - an intuitive new global index for determining the percentage of field loss,
Pattern deviation graphs - identifies local visual field loss, minimizing the effects of ocular media such as cataract,
STATPAC - compares results to proprietary age and glaucoma normative databases,
Kinetic, Custom and Social Security tests provide a wide range of special purpose test protocols,
HFA-NET Pro with EasyConnect RCT - provides plug-n-play connectivity solutions that improve office efficiency,
DICOM gateway option supports connectivity,
Touch screen and menu-driven interface for easy operation,
Ergonomic design for maximum comfort and versatility,
Network capabilities,
Customized prints,
Equipped with LEXMARK printer with paper roll diameter: 22 cm,
Polometer placed on SKF ACTUATION SYSTEM mobile table (4 wheels with brake) with electric height adjustment from: 68 to 100 cm,
Menu language selection: ENG, GER, ESP, FR, IT, JP, PT, SWE,
Included:
User manual in English (PDF),
Wired keyboard,
Wired mouse,
SKF ACTUATION SYSTEM mobile table,
LEXMARK printer,
Patient button
Power cord,
Dimensions: 110 x 60 x 150 / 182 cm,
Weight: 75 KG,
Cat 02,
It has a current inspection and is ready to work,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Possibility of extending the warranty for an additional fee to 12 months for the domestic and international market,
The warranty period does not cover bulbs and other light sources installed in the device,
Financing options (Poland only): Installments, Leasing, Loan,



PRAISTON

