



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordynator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Dental compressor EKOM DK50 2VS/M (with box, with membrane dryer) (Ex-Display)

New (exhibition),
Real product photos,
Slovak production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Power: 1.1 kW / 1.2 kW (3x400V/50 Hz),
Technical specifications:
Compressor efficiency (working pressure 5-7bar):
108 l.min- 1/5bar,
Tank capacity: 25 lit.,
Number of dental sets: 2,
Oil-free,
For power supply: two units,
Operation mode: S1-100%,
Noise level:
≤ 55 dB [A],
Air drying degree: dew point -20°C,
Included:
Power cord,
Mounting jar with magnet,
Magnetic jar with a capacity of 1 L.,
EKOM soundproofing cabinet,
Dimensions: 56 x 67.5 x 87 cm
Weight: 101 KG,
It has a current inspection and is ready to work,
Technical Passport (Service Report) issued valid for a period of 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Possibility of extending the warranty for an additional fee to 12 months for the domestic and international market,
Financing options (Poland only): Installments, Leasing, Loan,

