



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



Polometer (perimeter) CARL ZEISS HUMPHREY SYSTEM 720i (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real product photos,
Manufactured in the U.S.A.,
Power supply: 230 V,
Frequency: 50/60 Hz,
Bulb: Halogen 12 V / 30 W,
Software: 5.1.2.,
Technical specifications:
Field of view: 90°,
Maximum stimulus intensity: 10,000 ASB,
Stimulus duration: 200 ms,
Stimulus wavelength: Broadband visible light,
Canopy illumination: 31.5 ASB,
Testing distance: 30 cm,
Library of threshold tests:
24-2, 30-2, 10-2, Spot,
60-4,
Threshold test strategies:
SITA Standard, SITA Fast, Full Threshold, FastPac,
Screening Test Library:
Central Field Test Patterns: C40, C76, C80,
Peripheral Field Test Patterns: P-60, FF-81, FF-120, FF-135,
Screening Test Strategies: Dual Zone, Triple Zone, Quantify Defects,
Screening Test Modes: Dual Zone/Triple Zone and Defect Definition, Age-Related Level and Threshold Modes, Single Intensity,
Special Test Library:
Esterman Monocular,
Esterman Binocular,
Superior Room 36,
Superior Room 64,
Stimulus/Background Color: White on White,
General Test Features: Goldmann Stimulus Sizes: III,
User Defined Test Store,
Includes Built-in 11" Touchscreen Monitor,
Electric Chin Rest Adjustment: up-down and sideways,
Possibility to select the menu in the following languages: EN, DE, ES, FR, IT, JP, PT, SE,
The whole placed on the SKF ACTUATION SYSTEM mobile ophthalmic table:
With the possibility of height adjustment in the range: 67 - 100 cm,
Included:
User manual in English (PDF),
Power cord,
Patient button,
Wired keyboard,
Built-in PRINTEX printer
Dimensions:
Total: Total: 87 x 55 x 133/166 cm,
Weight: 84 KG,
Cat 03,
It has a current inspection and is ready to work,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6 months for the domestic market (Poland),
3 months for the international market,
Possibility to extend the warranty for up to 12 months for domestic and international markets,
The warranty period does not cover bulbs and other light sources installed in the device,
Financing options (Poland only): Installments, Leasing, Loan,

