



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **MELAG VACUKLAV 30-B autoclave (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Power: 2400 W,  
Pre-vacuum and fractional vacuum generated by a vacuum pump,  
Electronic LCD display,  
It has the following work programs:  
Universal program:  
134°C - 2.1 bar/3.5 min - wrapped metal tools,  
Quick program S:  
134°C - 2.1 bar/3.5 min - unwrapped metal tools,  
Quick program B:  
134°C - 2.1 bar/3.5 min - wrapped metal tools,  
Prion program:  
134°C - 2.1 bar/20 min - tools metal wrapped,  
Delicate program:  
121°C - 1.1 bar/15 min - wrapped tools, rubber articles, textiles, glass,  
The user can perform additional checks of the autoclave's operation by running the tests:  
Bowie & Dick: 134°C - 2.2 bar/3.5 min - test for water vapor permeability,  
Leakage test - vacuum test used to check the tightness of the autoclave,  
Recorder socket,  
Acoustic alarms,  
Chamber capacity: 17.6 liters,  
Chamber load capacity:  
Tools: up to 5 KG,  
Clothing: up to 2 KG,  
Menu in: German,  
Included:  
User manual in English (PDF),  
Power cord,  
MELADEM 40 water demineralizer + 2 new filters,  
New 2 perforated trays with dimensions: 30 x 22 x 1.5 cm,  
Tray stand + handle,  
Dimensions: 43 x 61 x 49 cm,  
Weight: 43 KG,  
Cat 03,  
It has a current inspection and is ready to work,  
Issued Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6 months for the domestic market (Poland),  
3 months for the international market,  
Possibility to extend the warranty for an additional fee to 12 months for the domestic and international market,  
Financing options (Poland only): Installments, Leasing, Loan,

