



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **CARL ZEISS OPMI 1-FC colposcope (video track) (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
o  
OPMI 1-FC is a mobile colposcope, equipped with a camera,  
o  
Specifications:  
Light source: 12V 100W halogen bulb,  
Infinitely adjustable light intensity,  
Fiber optic,  
Magnifications: 0.4 / 0.6 / 1 / 1.6 / 2.5,  
Focal length: f = 250,  
Eyepiece x12.5 with infinitely adjustable spacing,  
Built-in green filter,  
Infinitely adjustable light intensity with a knob,  
§  
Infinitely manual adjustment of the eyepiece height on the arm in the range: 50 - 150 cm,  
Colposcope expanded with a video track, which includes:  
CANON Model EOS M3 camera:  
Features a 22.3 x 14.9 mm CMOS sensor with 24.2 MP resolution,  
Large, bright touchscreen for clear images,  
Simple function controls and excellent low-light performance for capturing high-quality images,  
Image processor: DIGIC 6,  
Focus control: Hybrid CMOS AF II,  
ISO sensitivity: 100 - 12800,  
Auto white balance set by the sensor,  
3" sRGB Clear View LCD II touch screen,  
3:2 aspect ratio,  
Selectable menus in PL, EN, DE, FR, ES, RU, PT, CS, IT, FI, NL, SV, NO, HU, DA, TR, RO, AR,  
Support for SD, SDHC, SDXC cards,  
Video: Full HD, 30 fps,  
Images: RAW, JPEG,  
PHILIPS monitor:  
Screen diagonal: 21.5" inches,  
Resolution: 1920 x 1080 px,  
Matrix: LED TN,  
Mobile, on 5 - arm mobile base with casters, including 2 with brake,  
Includes:  
Power cord,  
CANON camera battery 7.5 Wh,  
CANON LC-E17E Charger,  
SMART CHARGER USB charger ,  
16 GB SDHC memory card,  
Wi-Fi card,  
Camera user manual in Polish (PDF),  
Overall dimensions: 90 x 65 x 132 cm,  
Weight: 60 KG,  
Has an up-to-date inspection and is ready for use,  
Issued Technical Passport (Service Report) valid for a period of 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,  
The warranty period does not include bulbs and other light sources installed in the device,  
Possibility of financing (Poland only): Installments, Leasing, Loan,

