



PRAISTON Sp. z o.o.
ul. Górowska 32
64-100 Leszno
Polska

Biuro: +48 65 527 01 67
Serwis: +48 782 844 000
Fax: +48 65 527 01 67

E-mail: biuro@praiston.pl

Koordinator ds. sprzedaży
Krzysztof Wybieralski
+48 882 762 006

kw@praiston.pl



COMINOX FLASH paper-foil package sealing machine (Reconditioned)

Reconditioned (used),
Technical condition: very good,
Visual condition: very good,
Real photos of the product,
Italian production,
Power supply: 230 V,
Frequency: 50/60 Hz,
Power: 100 W,
COMINOX FLASH
- impulse electronic welder,
Sealer working in a continuous cycle at a constant temperature,
Technical specifications:
Weld width: 10 mm,
Maximum sleeve width: 250 mm,
Automatic temperature control,
Width of sleeve bar: 26 cm,
Weld width: 12 mm,
Built-in cutter,
Cooling time not needed between sealing operations,
Wall-mountable,
Included:
Power cord,
Dimensions: 5.8 KG,
Weight: 44.5 x 32.5 x 20.5 cm,
Has a current inspection and is ready for operation,
Issued Technical Passport (Service Report) valid for 12 months,
Warranty:
6-months for domestic market (Poland),
3-months for the international market,
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,
Financing options (Poland only): Installments, Leasing, Loan

