



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordinator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



**CARL ZEISS KSK 150-FC colposcope (video track) (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
German production,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Power: 150 VA  
ZEISS KSK 150-FC  
Is a mobile colposcope equipped with a video track,  
Light source: halogen bulb 12V / 100W,  
Infinitely adjustable light intensity,  
Fiber optic,  
Green filter,  
Magnification: 0.4x, 0.6x, 1x, 1.6x, 2.5x,  
Focal length (f): 250,  
Eyepiece: 20x,  
Infinitely adjustable:  
Eyepiece height from 74 -120 cm,  
Eyepiece spacing by means of knobs,  
There are knobs on the pantographic arm to lock it in the selected position,  
Colposcope expanded with a video track, which includes:  
CANON Model EOS M3 camera:  
Features a 22.3 x 14.9 mm CMOS sensor with 24.2 MP resolution,  
Large, bright touchscreen for clear images,  
Simple function controls and excellent low-light performance for capturing high-quality images,  
Image processor: DIGIC 6,  
Focus control: Hybrid CMOS AF II,  
ISO sensitivity: 100 - 12800,  
Auto white balance set by the sensor,  
3" sRGB Clear View LCD II touch screen,  
3:2 aspect ratio,  
Selectable menus in PL, EN, DE, FR, ES, RU, PT, CS, IT, FI, NL, SV, NO, HU, DA, TR, RO, AR,  
Support for SD, SDHC, SDXC cards,  
Video: Full HD, 30 fps,  
Images: RAW, JPEG,  
FUJITSU E22T-7 monitor:  
Monitor diagonal: 21,5",  
Resolution: 1920 x 1080 px,  
Dimensions: 52 x 31 x 6 cm,  
Placed on a movable arm,  
Has the following inputs and outputs:  
D-Sub (VGA),  
DVI,  
HDMI,  
SPEAKER,  
Mobile, on a 5-arm mobile base with casters, including 2 with brakes,  
Includes:  
CANON battery for the camera 7.2 V / 1040 mAh,  
NEWELL LP-E17 battery for camera 7.2 V / 950 mAh,  
16GB microSD card,  
SDHC + wi-fi adapter,  
HDMI mini cable,  
LC-E17E Charger,  
Newell USB charger,  
Colposcope instruction manual in English (PDF),  
Camera instruction manual in Polish (PDF),  
Power cord,  
Overall dimensions: 90 x 65 x 132 cm,  
Weight: 57 kg,  
Cat 06,  
Has an up-to-date inspection and is ready for operation,  
Issued Technical Passport (Service Report) valid for a period of 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty up to 12-months for domestic and international market for a surcharge,  
Financing options (Poland only): Installments, Leasing, Loan,

