



**PRAISTON Sp. z o.o.**  
ul. Górowska 32  
64-100 Leszno  
Polska

Biuro: +48 65 527 01 67  
Serwis: +48 782 844 000  
Fax: +48 65 527 01 67

E-mail: [biuro@praiston.pl](mailto:biuro@praiston.pl)

Koordynator ds. sprzedaży  
Krzysztof Wybieralski  
+48 882 762 006

[kw@praiston.pl](mailto:kw@praiston.pl)



## **SMR MAXI SELECT S2800000 Ophthalmic Chair (Reconditioned)**

Reconditioned (used),  
Technical condition: very good,  
Visual condition: very good,  
Real photos of the product,  
Manufactured by U.S.A.,  
Power supply: 230 V,  
Frequency: 50/60 Hz,  
Upholstery with medical approval in blue (possibility to replace the upholstery with a new one, from our color pattern for an additional fee),  
SMR MAXI SELECT armchair  
is a multifunctional chair ideally suited for ophthalmology and ENT surgeries, and through built-in functions can be used as a treatment chair,  
Technical specifications:  
Electric control of the chair through built-in side panel on both sides:  
Chair back tilt in the range (automatic synchronization of the leg rest with the back rest): 80° / 0° / -8°,  
Seat height adjustment in the range: 53 - 96 cm,  
Possibility to put the chair in the reclining position,  
Built-in programmable button with the ability to assign the selected position,  
Built-in programmable button with preset sitting position,  
Electric locking of the seat rotation around its own axis,  
Manual functions:  
Retractable armrests on both sides,  
Ability to rotate the chair around its own axis 270°,  
Free adjustment of the patient's headrest,  
Included:  
Power cord,  
Dimensions:  
Headrest: 25 x 23 cm,  
Back rest: 48 x 60 cm,  
Seat: 50 x 45 cm,  
Leg rests: 42 x 32 cm,  
Patient step: 28 x 21 cm,  
Total: 80 x 75 x 110/153 cm,  
Weight: 120 KG,  
Has up-to-date inspection and is ready for operation,  
Issued Technical Passport (Service Report) valid for 12 months,  
Warranty:  
6-months for domestic market (Poland),  
3-months for the international market,  
Possibility to extend the warranty at a surcharge to 12-months for domestic and international markets,  
The warranty period does not include bulbs and other light sources installed in the device,  
Possibility of financing (Poland only): Installments, Leasing, Loan,

